

Product sheet



LCS³ LEGRAND

LCS³ 19" PDU 1U 6 x 2P+E french standard with 3m power supply cord and equipped with a RCBO 30mA

REF. 646833 | EAN. 3414970765543

> [Visit e-catalogue](#)

Product characteristics

- Single phase
- 6 x 2P+E french/belgian standard outlets equipped with protective shutters
- Input voltage 230V
- Input current 16A
- Maximum power 3,7kW

The product's benefits

Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

Usage


- Equipped with a 1P RCBO (Residual Current Circuit Breaker with Overload) C16 6kA 30mA AC type C curve (ref. 410705) for protecting equipment against short-circuits and overloads and protecting people against leakage currents

Avantages

- Angle of outlets is 55°

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-14.pdf | PDF (3.13Mo)

 S000093176FR-14.pdf | PDF (3.14Mo)

Agreements & Certificates

 LGRP-01740-V01.01-EN.pdf | PDF (0.91Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1016.pdf | PDF (0.19Mo)