

# Product sheet



## LCS<sup>3</sup> LEGRAND

LCS<sup>3</sup> 19" PDU 1U 6 x 2P+E french standard with 3m power supply cord and equipped with a SPD and a luminous switch

REF. 646835 | EAN. 3414970765567

PDU 19 inches 1U with 6 x 2P+E french standard outlets, to supply power to equipment in 19 inches enclosures. With aluminium casing, socket modules, a mounting and a termination solution. With additional SPD.

> [Visit e-catalogue](#)

## Description

PDU 19 inches 1U with 6 x 2P+E french standard outlets, to supply power to equipment in 19 inches enclosures. With aluminium casing, socket modules, a mounting and a termination solution. With additional SPD.

### Product characteristics

- Single phase
- 6 x 2P+E french/belgian standard outlets equipped with protective shutters
- Input voltage 230V
- Input current 16A
- Maximum power 3,7kW

### Recommendation / Restriction

- SPD (Surge protective devices) are designed to be installed at use points and have to be used in combination with a voltage surge protector installed in the panel. SPD are not designed to provide sole protection for an installation in a building likely to be hit by direct lightning strikes (e. g. buildings equipped with lightning arresters). This would immediately put the device out-of-order by exceeding its maximum discharge capacity.

## Documentation

### TECHNICAL DOCUMENTATION

S000093176EN-15.pdf | PDF (3.09Mo)

LE09269AA-04.pdf | PDF (1.89Mo)

S000093176FR-15.pdf | PDF (3.1Mo)

### Agreements & Certificates

LGRP-01741-V01.01-EN.pdf | PDF (0.9Mo)

## The product's benefits

### Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

### Usage

- Equipped with an additional SPD (Surge Protective Devices) designed to limit transient overvoltages of atmospheric and industrial origin. LED switch function to control the PDU power supply : a white LED is lit when the PDU sockets are supplied with power.

### Avantages

- Angle of outlets is 55°

### CATALOGUE PAGE & OTHERS

ex223001\_1016.pdf | PDF (0.19Mo)



LGRP-01741-V01.01-FR.pdf | PDF (0.86Mo)