

Product sheet



VALENA LIFE LEGRAND

Cover plate Valena Life - electronic room thermostat - with mechanism - white

REF. 752133 | EAN. 3414970540966

> [Visit e-catalogue](#)

Product characteristics

- Valena™ Life - motion sensors, roller blind controls and thermostats with cover plate - Valena In'Matic mechanisms supplied with cover plates and support frames - To be equipped with plates - Supplied with mounted dust protection transparent shield - Flowpack packaging: robust protection to ensure optimum operation
- Thermostats - Screw terminals Electronic room thermostats - Control knob with index and adjustable segments for min. and max. settings - Adjustable range from 5°C to 30°C (+/- 0.5°C) - Power supply: 230 V~ - 50/60 Hz - One potential-free changeover contact output - Suitable for controlling heated ceilings and underfloor heating - LV use breaking capacity: - 8 A - 250 VA- resistive inductive circuit - 2 A - 250 VA- inductive circuit - ELV use breaking capacity: - 12 to 48 VA- 12 to 24 V=, from 1 mA min. to 500 mA max. - For thermostat: - - Electronic room thermostat - Supplied with mechanism

Documentation

TECHNICAL DOCUMENTATION

- [LE07426AE.pdf](#) | PDF (1.58Mo)
-  [F03354EN-00.pdf](#) | PDF (0.34Mo)

CAD & Design specs / BIM

-  [752133_AllCATPart.stp](#) | IFC (21.08Mo)