

Product sheet



VALENA LIFE LEGRAND

Push-dimmer Valena Life - 240 V~ - 50 Hz - with cover plate - white

REF. 752162 | EAN. 3414970465177

[> Visit e-catalogue](#)

Product characteristics

- Valena™ Life - dimmers with cover plate - Valena In'Matic mechanisms supplied with cover plates and support frames - To be equipped with plates - Supplied with mounted dust protection transparent shield - Flowpack packaging: robust protection to ensure optimum operation
- Dimmers 240 V~ - 50 Hz - Equipped with overvoltage and short-circuit protection - When switched on, lights up at the level set before last switch-off - Can be remotely controlled via non-illuminated push-buttons (Cat.No 7 520 11), with each push-button able to perform the ON/OFF and dimming functionPush-dimmer without neutral - For all types of lamps: - dimmable LEDs: 5 W to 75 W (10 lamps max.) - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.) - halogen with ferromagnetic or electronic transformer: 3 VA to 400 VA - fluorescent tube - ballast: 3 VA to 200 VA - halogen and incandescent 240 V~: 3 W to 400 W - When switched on, gradually (2 seconds) lights up at the level set before last switch-off - Functioning: - dimming mode - pre-set level mode (0%, 33%, 66% and 100%) - nightlight mode: dimming of the lamp for 1 hour - White

Documentation

TECHNICAL DOCUMENTATION

- [LE08593AA_imp.pdf](#) | PDF (0.21Mo)
- 📄 [F01602FR-06.pdf](#) | PDF (0.88Mo)
- [LE07457AC.pdf](#) | PDF (1.2Mo)
- 📄 [F01602EN-06.pdf](#) | PDF (0.79Mo)