

# Product sheet



DLP LEGRAND

Full assembled DLP Trunking, 2 compartments, cover 65mm, 50x150mm. White

REF. 010427 | EAN. 3245060104276

[> Visit e-catalogue](#)

## Product characteristics

- Maximum sections : 3060mm<sup>2</sup> for each compartment
- Composed with 2 compartments body and 2 unique flexible covers (65mm width), delivered in 6 units of 2m
- Can be used with Mosaic/Arteor ranges
- Integrated partition (no additional installation) Possibility to adapte a removable separation partition
- Comply with reliability, safety and technical performance requirements accord EN50085-2-1

## The product's benefits

### Installation

- Fixing by: gluing (Neoprene glue (cat.no 030949), wall plug (cat.no 030898, 030899), DLP rapid wall plug (ref 0308 97), Spit end (cat.no 010695) or screw, nails... For cutting all plastic bodies, use a saw or a DLPlus cutting unit for PVC DLP (ref. 0 306 98)

### Usage

- Full assembled DLP Trunking offers a perfectly flexible installation over time.

## Documentation

### TECHNICAL DOCUMENTATION

 F00885EN-04.pdf | PDF (1.66Mo)

 F00885FR-03.pdf | PDF (1.99Mo)

### CAD & Design specs / BIM

BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt | RVT (23.93Mo)

BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt | RVT (14.36Mo)

BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt | RVT (13.17Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_1074-1075.pdf | PDF (0.12Mo)

 ex223001\_1071.pdf | PDF (0.11Mo)

### Agreements & Certificates

 LGRP-01605-V02.01-EN.pdf | PDF (0.75Mo)

 NF 004-601796A | (0.42Mo)

 LGRP-01605-V02.01-FR.pdf | PDF (0.71Mo)