

# Product sheet



DLP LEGRAND

Full assembled DLP Trunking, 1 compartment, cover 65mm, 50x80mm. White

REF. 010462 | EAN. 3245060104627

[> Visit e-catalogue](#)

## Product characteristics

- Maximum section : 3340mm<sup>2</sup>
- Composed with 1 compartment body and 1 unique flexible cover (65mm width), delivered in 10 units of 2m
- Can be used with Mosaic/Arteor ranges
- Possibility to adapte a removable separation partition
- Comply with reliability, safety and technical performance requirements accord EN50085-2-1

## The product's benefits

### Installation

- Fixing by: gluing (Neoprene glue (cat.no 030949), wall plug (cat.no 030898, 030899), DLP rapid wall plug (ref 0308 97), Spit end (cat.no 010695) or screw, nails... For cutting all plastic bodies, use a saw or a DLPlus cutting unit for PVC DLP (ref. 0 306 98)

### Usage

- Full assembled DLP Trunking offers a perfectly flexible installation over time.

## Documentation

### TECHNICAL DOCUMENTATION

F00885FR-05.pdf | PDF (1.98Mo)

F00885EN-06.pdf | PDF (2.22Mo)

### CAD & Design specs / BIM

BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt | RVT (23.93Mo)

BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt | RVT (14.36Mo)

BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt | RVT (13.17Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_1074-1075.pdf | PDF (0.12Mo)

ex223001\_1070.pdf | PDF (0.1Mo)

### Agreements & Certificates

LGRP-01605-V02.01-EN.pdf | PDF (0.75Mo)

NF 004-601796A | (0.42Mo)

LGRP-01605-V02.01-FR.pdf | PDF (0.71Mo)