

Product sheet



LCS³ LEGRAND

LCS³ 19" PDU 1U 6 x C13 + 2 x C19 IEC 60320 standard with terminal block

REF. 646809 | EAN. 3414970765260

PDU 19 inches 1U with 10 x C13 outlets with cord locking system, designed for supplying power to equipment in 19 inches enclosures. It comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

> [Visit e-catalogue](#)

Description

PDU 19 inches 1U with 10 x C13 outlets with cord locking system, designed for supplying power to equipment in 19 inches enclosures. It comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

Product characteristics

- Single phase
- 6 x C13 + 2 x C19 IEC 60320 standard outlets with locking
- Input voltage 230V
- Input current 16A
- Maximum power 3.7kW

Recommendation / Restriction

- Maximum capacity of terminal block 6mm². Conforms to standard IEC 60320-2-2

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-14.pdf | PDF (3.13Mo)

 S000093176FR-14.pdf | PDF (3.14Mo)

Agreements & Certificates

 LGRP-01739-V01.01-FR.pdf | PDF (0.91Mo)

 LGRP-01739-V01.01-EN.pdf | PDF (0.95Mo)

The product's benefits

Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

Usage

- Cord locking system : the cord is locked mechanically into the outlet to prevent any unintended disconnection (caused by maintenance, vibrations, etc.). This universal solution is compatible with all standard cords available on the market.

Avantages

- Angle of outlets is 90°

CATALOGUE PAGE & OTHERS

 ex223001_1015.pdf | PDF (0.13Mo)