

Product sheet



VALENA LIFE LEGRAND

RJ45 socket category 6 STP with claws mat black
Valena Life

REF. 756346 | EAN. 3414972241045

[> Visit e-catalogue](#)

Product characteristics

- Category 6 STP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds. Shielded socket. Body and spreader made of metal alloy with copper/nickel coating.
- Claw fixing
- 2 modules
- Mat black
- Equipped with a protective dust cover.

Recommendation / Restriction

- Conform to standards ISO 11801 Edition 2, CENELEC EN 50173-1 2007, ANSI/TIA 568 C.2, ISO/IEC series 60603-7. Indoor use only. Clean the surface with a cloth. Do not use acetone, tar-removing cleaning agents or trichloroethylene.

The product's benefits

Installation

- Equipped with connectors with quick toolless connection : this system allows the wire pairs to be spread easily before mounting them on the connector.

Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

-  F02116EN-02.pdf | PDF (1Mo)
-  LE07456AC.pdf | PDF (5.97Mo)
-  F02116FR-02.pdf | PDF (1.01Mo)

