

# Product sheet



LEGRAND

Control interface for autotest/addressable luminaires  
LVS2 230 V~

REF. 062600 | EAN. 3245060626006



> [Visit e-catalogue](#)

## Product characteristics


- LVS2 (Legrand Vision System) - addressable and monitoring system
- Control interface for autotest/addressable luminaires - Centralises the operating state of addressable emergency lighting luminaires - Capacity : - Direct connection of 250 addressable luminaires to the control interface (star configuration or series connection) - The longest line is limited to 700 m - Extension via repeater Cat.No 0 626 03 for more than 250 addressable luminaires or a line longer than 700 m - Maximum capacity of the central control panel : 1023 addressable luminaires - Configuration software included (control interface settings and ID configuration for addressable luminaires) - To be completed with at least one of the following terminals : - PC with monitoring software Cat.No 0 626 02 - Touch screen controller Cat.No 0 626 01 - PC with internet navigator (limited functions) - Connections : - RJ 45 socket for IP network - terminals for RS 232 and RS 485 - Mini USB for PC local settings - Power supply : - 230 V~ - 50/60 Hz - Ni - Cd battery : 8.4 V - 0,15 Ah

## Documentation

### TECHNICAL DOCUMENTATION

- [LE05156AE\\_EN.pdf](#) | PDF (0.3Mo)
-  [GT\\_LE05022AF\\_EN.pdf](#) | PDF (24.42Mo)
-  [GT\\_LE05022AF\\_FR.pdf](#) | PDF (19.54Mo)
- [LE05156AE\\_FR.pdf](#) | PDF (0.64Mo)

### CAD & Design specs / BIM

-  [062600.dwg](#) | DWG (0.11Mo)

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0916.pdf](#) | PDF (0.08Mo)