

Product sheet



LCS³ LEGRAND

LCS³ 19" PDU 1U 9 x 2P+E french standard tamperproof red outlets with 3m power supply cord

REF. 646811 | EAN. 3414970765307

PDU 19 inches 1U with 9 x 2P+E french standard tamperproof red outlets, designed for supplying power to equipment in 19 inches enclosures. It comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

> [Visit e-catalogue](#)

Description

PDU 19 inches 1U with 9 x 2P+E french standard tamperproof red outlets, designed for supplying power to equipment in 19 inches enclosures. It comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

Product characteristics

- Single phase
- 9 x 2P+E french/belgian standard tamperproof red outlets equipped with protective shutters
- Input voltage 230V
- Input current 16A
- Maximum power 3.7kW

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-14.pdf | PDF (3.13Mo)

 S000093176FR-14.pdf | PDF (3.14Mo)

The product's benefits

Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

Avantages

- Angle of outlets is 55°

CATALOGUE PAGE & OTHERS

 ex223001_1015.pdf | PDF (0.13Mo)