

# Product sheet



LEGRAND

Standard LED emergency luminaire Twinspot - non autotest - 2 x 750 lm - 1h

REF. 661452 | EAN. 3414970575777

[> Visit e-catalogue](#)

## Product characteristics

- LED Twinspot emergency lighting luminaires - High performance LED non maintained emergency lighting luminaires - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs spotlights with optimized lighting distribution - Low consumption electronic switching power supply - High capacity terminals : 2 x 2.5 mm<sup>2</sup> - IP 55 - IK 07 - Duration : 1, 2 and 3 hours. Ni - Cd batteries. Recharge time : 24h - Green charge indicator with high luminosity LED, to improve visibility from the floor when high installation - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Rest mode with remote control device Cat.No 0 039 01 to avoid battery discharge in case of voluntary power cut - Surface mounting installation with 4 wall - mounting lugs (Cat.No 0 358 02, supplied) or 4 screws (not supplied)
- Standard LED spotlight luminaires - non-Maintained (NM) - 2 x 750 lm 1h

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE08274AD.pdf](#) | PDF (1.6Mo)

### Agreements & Certificates

[SDS - Battery NiCd JYH.pdf](#) | PDF (0.33Mo)

[ENEC-ENEC\\_1158/A1](#) | (0.64Mo)

[OC / CB-FR\\_717632/A1](#) | (0.82Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0912.pdf](#) | PDF (0.07Mo)