

Product sheet



LEGRAND

Standard luminaires U34 LED - 1h duration with opal diffuser - 250 lm

REF. 661160 | EAN. 3245066611600

[> Visit e-catalogue](#)

Product characteristics

- U34LED environment friendly - indoor self - contained emergency lighting luminaires LED - LED Maintained/non-maintained units - High power LEDs with specially designed lenses optimizing the lighting distribution - IP 42 - IK 07 - Class II - Power supply : 230 V \pm 10% - 50/60 Hz - Very low consumption switching power supply - Fully recyclable after removing - Environment friendly Ni - MH batteries - Removable plug - in plate to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5 mm² - Charge monitor with a green LED - Can be equipped with metallic protection grids Cat.Nos 0 626 92/93
- Standard luminaires - Maintained/non-maintained (M/NM) - Standard luminaires incorporate an external manual lamp test with testing tool Cat.No 6 612 991 h duration with transparent diffuser - 250 lm - 1h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

- LE04859AB.pdf | PDF (1.77Mo)
- 📄 S000082232FR-2.pdf | PDF (8.01Mo)

Agreements & Certificates

- 📄 OC / CB-690885 | (1.17Mo)
- 📄 LGRP-2015-295-V1-EN.pdf | PDF (0.61Mo)

CATALOGUE PAGE & OTHERS

- ⚙️ Legrand 661160 U34LED 250LM-1H M.zip | ZIP
- 📄 ex223001_0908.pdf | PDF (0.06Mo)