

Product sheet



LEGRAND

Standard luminaires U34 LED - 3h duration with opal diffuser - 200 lm

REF. 661190 | EAN. 3245066611907

[> Visit e-catalogue](#)

Product characteristics

- U34LED environment friendly - indoor self - contained emergency lighting luminaires LED - LED Maintained/non-maintained units - High power LEDs with specially designed lenses optimizing the lighting distribution - IP 42 - IK 07 - Class II - Power supply : 230 V \pm 10% - 50/60 Hz - Very low consumption switching power supply - Fully recyclable after removing - Environment friendly Ni - MH batteries - Removable plug - in plate to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5 mm² - Charge monitor with a green LED - Can be equipped with metallic protection grids Cat.Nos 0 626 92/93
- Standard luminaires - Maintained/non-maintained (M/NM) - Standard luminaires incorporate an external manual lamp test with testing tool Cat.No 6 612 991 h duration with transparent diffuser - 200 lm - 3h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

→ [LE04859AB.pdf](#) | PDF (1.77Mo)

Agreements & Certificates

[OC / CB-690885](#) | (1.17Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0908.pdf](#) | PDF (0.06Mo)

[Legrand 661190 U34LED 200LM-3H M.zip](#) | ZIP