

# Product sheet



## CX3 WITH NETATMO LEGRAND

### CX3 with Netatmo Module Control

REF. 412181 | EAN. 3414971795600

> [Visit e-catalogue](#)

## Product characteristics

- WiFi 2,4 GHz 802.11 b/g/n Open/WEP/WPA/WPA 2 - personal (TKIP and AES)
- Compatible with Apple Home Kit, Google Assistant and Amazon Alexa.
- 2,5 modules wide (45mm)

## Recommendation / Restriction

- A WiFi connection via your Internet home box is required. Upgrade your smart home by adding other Legrand "with Netatmo offers": other electrical panelboard modules, switches & power outlets, wireless on-wall switches ....
- WiFi 2,4 GHz 802.11 b/g/n Open/WEP/WPA/WPA 2 - personal (TKIP and AES)
- Compatible with Apple Home Kit, Google Assistant and Amazon Alexa.

## The product's benefits

### Installation

- The Module Control can be easily installed in any standard DIN panelboard. Each house you wish to connect requires the installation of a single Control module on the electrical panel.

### Usage

- Define one or more schedules for remotely controlling on and off your appliances and monitor their consumption from your smartphone.

### Avantages


- Plan your energy savings! Define one or more schedules for switching your appliances on and off, very easily from the Home + Control app.
- In Home+Control app, get the possibility to create personalized scenario: daily/weekly/specific event such as "holidays" ...


## Documentation

### TECHNICAL DOCUMENTATION

→ [LE12071AC\\_1\\_FR.pdf](#) | PDF (2.43Mo)

→ [LE12071AC\\_EN.pdf](#) | PDF (2.42Mo)







 [F03038EN-02 \(Gateway module\).pdf](#) | PDF (0.76Mo)

 [F03038FR-02 \(Module Control\).pdf](#) | PDF (0.77Mo)

### Agreements & Certificates

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0112.pdf](#) | PDF (0.1Mo)

-  OC / CB-FR\_715670/A1 | (0.37Mo)
-  OC / CB-FR\_715847 | (0.31Mo)
-  OC / CB-FR\_715717/A1 | (0.22Mo)
-  NF-NF012\_3521/A1 | (0.54Mo)
-  NF-NF012\_3529/A1 | (0.55Mo)
-  Decl. UE RED-A 9095 A | (0.08Mo)