

# Product sheet



LEGRAND

Emergency luminaire URA ONE - standard  
Maintained/Non maintained - 1h - 200 lm - LED

REF. 661633 | EAN. 3414970312259

[> Visit e-catalogue](#)

## Product characteristics

- URA ONE - indoor self - contained emergency lighting luminaire LED - LED non-maintained and maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs with optimized lighting distribution - Low consumption switching power supply. Fully recyclable - Plug - in back with pre - cutted holes grid to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5mm<sup>2</sup>. IP 42 - IK 07 - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours. Charge monitor with a green LED. Opal diffuser - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Flat flush-mounting integration into ceiling and wall with flush-mounting frame Cat.Nos 6 616 50/51 - Decorative frame to enhance surface - mounting aesthetic integration Cat.Nos 6 616 54/55
- Standard luminaires - Require normal lighting manual switching off in order test emergency lighting Maintained/non-maintained (M/NM) - Can also operate in non-maintained mode according to the wiring of normal lighting - 200 lm - 1h (LEDs)

## Documentation




### TECHNICAL DOCUMENTATION

-  S000083576FR-3.pdf | PDF (3.97Mo)
-  S000083576EN\_3.pdf | PDF (4.07Mo)
-  LE06557AF.pdf | PDF (1.85Mo)




### CAD & Design specs / BIM

-  Legrand\_Emergencia\_URA\_ONE\_EXPORT\_EN.rfa | RFA (1.74Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0907.pdf | PDF (0.06Mo)
-  Legrand 661633 URAONE 200LM-1H M.zip | ZIP
-  ex223001\_0906.pdf | PDF (0.09Mo)

### Agreements & Certificates

-  LGRP-00660-V01.01-EN.pdf | PDF (0.61Mo)
-  ENEC-ENEC/000994 | (0.5Mo)
-  AENOR-007/001689 | (0.39Mo)