

Product sheet



LEGRAND

Rotating and fixable multi-outlet extension 6 sockets with cable 3m and 1,5mm² section

REF. 694540 | EAN. 3414971945029

[> Visit e-catalogue](#)

Product characteristics

- Multi-outlet extension with 6 flush 2P+T sockets with Schuko standard, 16A, 230V, 3680W. multi-outlet extension swivelling every 12° to the right or left compared to a horizontal installation.
- One 90° socket to connect a transformer without blocking another socket. Other sockets being oriented at 45°
- Blue illuminated ON / Off switch. Bi-colour Multi-outlet extension: white and black / dark grey

Recommendation / Restriction

- Indoor use

The product's benefits

Installation

- Multi-outlet extension with several installation possibilities.

Usage

- 3 installation possibilities: - product fixed to the wall (by screws not supplied) - product fixed by a cable tie (not supplied) - placed product

Avantages

- New: Multi-outlet extensions are fitted with flush sockets, thus ensuring an aesthetic product and preventing dirt from getting on the wells.
- Multi-outlet extension swivelling every 12° to the right or left compared to a horizontal installation.

Documentation

TECHNICAL DOCUMENTATION

F03127FR-00.pdf | PDF (0.21Mo)

F03127EN-00.pdf | PDF (0.2Mo)

Agreements & Certificates

OC / CB-FR_710045/M1 | (0.88Mo)

MEEI-UP 69265087 | (1.06Mo)

CATALOGUE PAGE & OTHERS

ex223001_0831.pdf | PDF (0.17Mo)