

Product sheet



NILOÉ™ LEGRAND

Double USB charging socket Niloé - ivory

REF. 764694 | EAN. 3414970804808

> [Visit e-catalogue](#)

Product characteristics

- Nilo - USB charging sockets - Mechanisms supplied with support frame and cover plate - Fixing with screws or claws (supplied) - For installation in flush-mounting box depth 40 mm minimum - Supplied cordless
- USB Type A charging sockets - 5 V - 3 A - 12 W - For recharging portable device - Conform to IEC 62684 - 2011 - 01 - Surge protection greater than 1 kV - Consumption in passive mode less than 0,06 W - Power supply AC/DC efficiency at highest Level (VI) - 2x2.5 mm² screw terminals - Class II SELV - Supplied cordless Double USB sockets - 2 modules - For fast charging smartphones and tablet PC - Ivory

Documentation

TECHNICAL DOCUMENTATION

 F02165EN-01.pdf | PDF (0.24Mo)

 F02165FR-01.pdf | PDF (0.23Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0748.pdf | PDF (0.13Mo)