

# Product sheet



LCS<sup>3</sup> LEGRAND

Patch cord fibre optic OM4 multimode Core SC/SC duplex 3 meters

REF. 032262 | EAN. 3414972057981

Patchcords provide flexible interconnection to active equipment, passive optical devices and cross-connects. Zirconia ferrule connectors manufactured with precision factory mounting and polishing techniques insure high transmission quality

> [Visit e-catalogue](#)

## Description

Patchcords provide flexible interconnection to active equipment, passive optical devices and cross-connects. Zirconia ferrule connectors manufactured with precision factory mounting and polishing techniques insure high transmission quality

### Product characteristics

- OM4 multi-mode SC/SC duplex
- Insertion loss max = 0,25dB
- High transmission quality thanks to premium range physical contact or ultra physical contact zirconia ferrule connectors.
- Zipcord LSZH (Low Smoke Zero Halogen) aqua sheaths
- Length 3m

### Recommendation / Restriction

- Legrand optic fibre patchcords are suitable for low loss datacom, data centre and some critical applications. Conform to IEC, ANSI-TIA, and Telecordia performances requirements

## Documentation

### TECHNICAL DOCUMENTATION

 F01339EN-09.pdf | PDF (0.15Mo)

 F01339FR-09.pdf | PDF (0.18Mo)

### Agreements & Certificates

 LGRP-01765-V01.01-EN.pdf | PDF (0.87Mo)

## The product's benefits

### Installation

- Patchcords are delivered in A to B configuration. Polarity on LC connectors can be switched on the field with a tool to make A to A patchcords.

### CATALOGUE PAGE & OTHERS

 ex223001\_1004.pdf | PDF (0.06Mo)