

Product sheet



MARINA LEGRAND

Marina 1460x800x463mm - IP66 IK10

REF. 036285 | EAN. 3245060362850

> [Visit e-catalogue](#)

Product characteristics

- IP 66 according to the standard EN/IEC 60529 : completely protected against dust and against jets of water of similar force to heavy seas
- Excellent resistance to corrosion and chemical agents : 1500h resistance to salt spray
- One-piece molded body, reversible cabinet
- RAL 7035 suitable for industrial environments

Recommendation / Restriction

- Recommended for industrial environments with aggressive constraints : corrosion and harsh weather conditions.

The product's benefits

Installation






- Double-bar lock. Equipped with universal lugs at the rear of the cabinets to facilitate the installation of accessories Autocentric of equipments

Usage


- Can be equipped with a wide range of dedicated accessories : plain or perforated plates, plinths, cable-entry plates, plain or glass doors, etc.


Documentation

TECHNICAL DOCUMENTATION

-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  041650-02.pdf | PDF (1.51Mo)
-  F01090FR-01.pdf | PDF (0.9Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)
-  F01090EN-01.pdf | PDF (0.93Mo)

CAD & Design specs / BIM

 Legrand-Industrial_enclosures-Polyester-Marina_enclosures-Plain_door.rfa | RFA (0.93Mo)


 036285.dwg | DWG (0.08Mo)

 Legrand-Enveloppes_industrielles-Polyester-Armoires_Marina-Porte_pleine.rfa | RFA (0.93Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0424.pdf | PDF (0.12Mo)
-  ex223001_0428.pdf | PDF (0.39Mo)
-  ex223001_0426-0427.pdf | PDF (0.36Mo)

Agreements & Certificates

-  VERITAS (BV)-07327/E0 BV | (0.59Mo)
-  OC / CB-FR 716848 | (0.38Mo)