

# Product sheet



## ATLANTIC LEGRAND

### Atlantic steel cabinet 1000x600x250mm - IP66 IK10

REF. 036932 | EAN. 3414970696601

> [Visit e-catalogue](#)

## Product characteristics

- IP 66 according to the standard EN/IEC 60529 : completely protected against dust and against jets of water of similar force to heavy seas
- Excellent resistance to corrosion and chemical agents thanks to textured polyester coating : 1000h resistance to salt spray
- One-piece welded body, reversible door, equipped with a cable - entry plate
- RAL 7035 suitable for industrial environments

## Recommendation / Restriction

- Recommended for industrial environments without any particular constraints.

## The product's benefits

### Installation






- Joinable cabinets. Reversible door. Double-bar lock. Equipped with universal lugs at the rear of the cabinets to facilitate the installation of accessories Autocentric of equipments

### Usage




- Can be equipped with a wide range of dedicated accessories : plain or perforated plates, plinths, cable-entry plates, plain or glass doors, etc.

## Documentation


### TECHNICAL DOCUMENTATION

-  EXB22009\_Flipbook\_FR\_(03\_2022).pdf | PDF (6.2Mo)
-  F02118FR-03.pdf | PDF (5.41Mo)
-  F02118EN-03.pdf | PDF (5.4Mo)
-  LE08301AA-01.pdf | PDF (0.77Mo)
-  EXB22010\_Flipbook\_EN\_(03\_2022).pdf | PDF (6.56Mo)





### CAD & Design specs / BIM

-  Legrand\_Atlantic\_vertical\_version\_references\_036910\_to\_036950.rfa | RFA (3.9Mo)
-  035517.dwg | DWG (0.06Mo)
-  Legrand\_Atlantic\_version\_verticale\_références\_036910\_à\_036950.rfa | RFA (3.9Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0416.pdf | PDF (0.06Mo)
-  ex223001\_0420-0421.pdf | PDF (0.28Mo)

### Agreements & Certificates

-  TUV GS-R 60175536 | (1.67Mo)
-  VERITAS (BV)-03212/J0 BV | (0.59Mo)
-  OC / CB-FR703246 | (0.59Mo)
-  UL listed cULus-E164087-19951122 | (0.84Mo)



036932.dwg | DWG (0.07Mo)



LGRP-2015-020-V1-EN.pdf | PDF (0.61Mo)