

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - PIR 140° motion sensor - IP42 - surface wall mounting motion

REF. 048942 | EAN. 3414970595249

> [Visit e-catalogue](#)

Product characteristics

- PIR detection 140°, range 8mx6m at 2.5m height
- IP42
- Switching control (3 - wire with neutral)
- Standby consumption: 0.75 W
- Cardboard

Recommendation / Restriction

- Voltage 230VAC 50/60Hz only

The product's benefits

Installation

- For direct surface-mounting on wall

Usage

- Ideal for passage areas without natural light

Advantages

- Cost effective solution
- Automatic switch-on taking into account the ambient light level
- Easy basic settings through a simple screw driver

Documentation

TECHNICAL DOCUMENTATION

- LE07907AC.pdf | PDF (1.97Mo)
- 📄 S000087128FR-3.pdf | PDF (1.51Mo)
- 📄 S000087128EN-2.pdf | PDF (1.51Mo)

CAD & Design specs / BIM

Legrand_Gestion_eclairage_Detect_mvt_autonome_140D_Mur.rfa
| RFA (0.54Mo)

Legrand_Lighting_Management_Standalone_Motion_Sensor_140D_Wall.rfa | RFA (0.54Mo)

📄 2D-LG-003513.zip | ZIP (0.85Mo)

CATALOGUE PAGE & OTHERS

📖 ex223001_0885.pdf | PDF (0.07Mo)

Agreements & Certificates

📄 LGRP-00152-V01.01-EN.pdf | PDF (0.56Mo)

📄 OC / CB-685326 | (0.52Mo)