

# Product sheet



## HYPRA LEGRAND

Panel mounting socket Hypira - IP 44 - 20/25 V~ - 16 A  
- 2P - plastic

REF. 052401 | EAN. 3245060524012

> [Visit e-catalogue](#)

## Product characteristics

- Hypira IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C ( - 20°C for Prinsinter) ELV panel mounting sockets 20 to 25 V~ - 50/60 Hz - 16 A 2P - To be associated with surface - mounting box Cat.No 0 524 19 for surface - mounting socket - Plastic - Pack = 5 - 16 A

## Documentation

### TECHNICAL DOCUMENTATION

 F00138FR-04.pdf | PDF (1.44Mo)

 F00138EN-04.pdf | PDF (1.25Mo)

### CAD & Design specs / BIM

LEGRAND\_PRISES\_NON\_VERROUILLEES\_ENCASTREES\_IP44\_20.rfa  
| RFA (0.86Mo)

 052401.dwg | DWG (0.13Mo)

LEGRAND\_NON\_INTERLOCKED\_SOCKETS\_SURFACE\_MOUNTED\_I  
P44\_20.rfa | RFA (0.6Mo)

LEGRAND\_NON\_INTERLOCKED\_SOCKETS\_FLUSH\_MOUNTED\_IP44  
\_20.rfa | RFA (0.86Mo)

LEGRAND\_PRISES\_NON\_VERROUILLEES\_SAILLIES\_IP44\_20.rfa  
| RFA (0.6Mo)

## Agreements & Certificates

 OC / CB-FR\_710635/A1 | (0.72Mo)