

Product sheet



MOSAIC™ LEGRAND

Back box for flush floor box in concrete floor

REF. 089604 | EAN. 3245060896041

[> Visit e-catalogue](#)

Product characteristics

- For integration of flush floor box (Ref. 6 896 22/23 and 088056) in concrete floor
- To be fixed on the slab
- Opercules to fold allowing the gripping of the floor box protection - Duct maximum height 38mm and maximum width 225mm - Ø20 to 25mm
- Back boxes made in galvanised steel (Z275) and Zamak

Recommendation / Restriction

- For installation in concrete floor only - Temperature of use, transport and storage: -5° à +60°

Documentation

TECHNICAL DOCUMENTATION

- [LE06866AA.pdf](#) | PDF (1.46Mo)
- [F02080EN-04.pdf](#) | PDF (1.22Mo)
- [F02080FR-04.pdf](#) | PDF (1.28Mo)
- [F01020EN-02.pdf](#) | PDF (1.34Mo)

CAD & Design specs / BIM

- [Legrand-ip44-floor-boxes-EN.rfa](#) | RFA (1.02Mo)
- [Legrand-boites-de-sol-ip44-FR.rfa](#) | RFA (1.02Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_1162.pdf](#) | PDF (0.06Mo)
- [ex223001_1160.pdf](#) | PDF (0.21Mo)
- [ex223001_1158.pdf](#) | PDF (0.09Mo)
- [ex223001_1159.pdf](#) | PDF (0.06Mo)
- [ex223001_1161.pdf](#) | PDF (0.11Mo)

Agreements & Certificates

- [LGRP-01205-V01.01-EN.pdf](#) | PDF (0.62Mo)
- [LGRP-01290-V01.01-EN.pdf](#) | PDF (0.61Mo)