

Product sheet



P 17 TEMPRA LEGRAND

Base up to 2 sockets for combined unit P17 - 16 A -371 x 125 mm

REF. 058938 | EAN. 3245060589387

[> Visit e-catalogue](#)

Product characteristics

- P17 Temptra combined units to be composed - IK 08 according to IEC 62262 - Self - extinguishing : 650 °C - Max. IP 66 Combined units height 220 mm to 441 mm Base for 220 x 125 mm faceplates - max. IP 66 - Base up to 2 sockets 16 A - Rail 5 modules 17.5 mm - External dimensions (Height x Width) : 371 x 125 mm

Documentation

TECHNICAL DOCUMENTATION

F00140EN-05.pdf | PDF (1.34Mo)

F00140FR-05.pdf | PDF (1.34Mo)

CAD & Design specs / BIM

058938.dwg | DWG (0.07Mo)