

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 1 gang 2-way switch - 10AX - Glossy gold

REF. 833401 | EAN. 3414970667724

[> Visit e-catalogue](#)

Product characteristics

- 10AX, 250V~
- Screw type terminals, marked for easy identification
- Large angled easy - to - access cable entries and captive screws
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Can be used as a simple switch but can also be associated with another two-way switch, thus allowing to turn the light on and off from two different control points.

Avantages


- Plate and rocker in same metal: Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes


Documentation

TECHNICAL DOCUMENTATION

 F02249EN-01.pdf | PDF (0.74Mo)

Agreements & Certificates

 ASTA-781 | (0.44Mo)

 OC / CB-FR_708093 | (0.72Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0722.pdf | PDF (0.09Mo)