

Product sheet



LEGRAND

MCCB DPX³ 1600 - thermal magnetic release - 3P - Icu 50 kA (400 V~) - In 1000 A

REF. 422265 | EAN. 3414970380319

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 1600 - thermal magnetic release MCCBs from 630 to 1250 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs thermal magnetic release fixed version - Thermal adjustable from 0,8 to 1 In - Magnetic adjustable from 5 to 10 In. Breaking capacity Icu 50 kA (400 V~) - 3P - In : 1000 A

Documentation

TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
- 📄 F01963FR01_DPX3_1600MT_FRAv3.pdf | PDF (0.71Mo)
- 📄 EXB15015_TG_Coordination_EN.pdf | PDF (5.41Mo)
- 📄 EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf | PDF (82.93Mo)
- 📄 F01963EN04_DPX31600_TM.pdf | PDF (1.64Mo)
- 📄 EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf | PDF (83.49Mo)

CAD & Design specs / BIM

- 📄 422262.dwg | DWG (0.17Mo)

CATALOGUE PAGE & OTHERS

- 📄 ex223001_0181.pdf | PDF (0.1Mo)
- 📄 ex223001_0198.pdf | PDF (0.03Mo)
- 📄 ex223001_0196-0197.pdf | PDF (0.52Mo)

Agreements & Certificates

- 📄 LGRP-00819-V01.01-EN.pdf | PDF (0.64Mo)