

# Product sheet



## LEGRAND

Redundancy function modules for stabilised switched modules power supply - max 20 A

REF. 146698 | EAN. 3414970543677

> [Visit e-catalogue](#)

## Product characteristics

- Stabilised switched mode power supplies - additional functions - Used to ensure optimum continuity of service for critical functions
- Redundancy function module - Can be used to control two 24 V= power supplies on the same load to ensure optimum continuity of service - Relay contacts and LED status indicators for the power supplies - For mounting on a symmetrical rail depth 7.5 mm and 15 mm - Input voltage : 21 to 28 V - Maximum rating : 20 A - Width : 56 mm

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE08164AA-01.pdf](#) | PDF (0.38Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0510.pdf](#) | PDF (0.03Mo)

[ex223001\\_0509.pdf](#) | PDF (0.03Mo)

[ex223001\\_0506.pdf](#) | PDF (0.08Mo)

[ex223001\\_0507.pdf](#) | PDF (0.06Mo)

## Agreements & Certificates

[UL listed cULus-E223674](#) | (0.04Mo)