

Product sheet



P 17 TEMPRA LEGRAND

Mobile socket P17 - IP44 - 200/250 V~ - 32 A - 2P+E

REF. 555214 | EAN. 3245065552140

[> Visit e-catalogue](#)

Product characteristics


- P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets , plugs , mobile sockets , appliance inlets and interlocked switched sockets
Mobile sockets - Cable clamping and closing without screws - Supplied unlocked 200/250 V~ - IP 44 32 A - 2P+E

Documentation


TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)




CAD & Design specs / BIM

-  555214.dwg | DWG (0.3Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0529.pdf | PDF (0.05Mo)
-  ex223001_0530.pdf | PDF (0.05Mo)
-  ex223001_0525.pdf | PDF (0.12Mo)
-  ex223001_0531.pdf | PDF (0.06Mo)

Agreements & Certificates

-  LGRP-2014-110-V1-EN.pdf | PDF (1.01Mo)
-  OC / CB-FR_710665 | (0.7Mo)
-  IMQ-CA02.05952 | (0.35Mo)