

Product sheet



LCS³ LEGRAND

Patch cord RJ45/RJ45 High Density category 6 U/UTP
LSZH blue 5m

REF. 051549 | EAN. 3414971438897

[> Visit e-catalogue](#)

Product characteristics

- Category 6 U/UTP : for up to 1 Gigabit per second data rate, unshielded cable
- 4,2mm outer diameter, AWG28
- Low Smoke Zero Halogen materials that emit limited smoke and no halogen when exposed to high sources of heat.
- 5 meter length
- Blue

Recommendation / Restriction

- Compliant with ANSI/TIA 568.2-D standard. Using this patchcord may have an impact on maximum authorized channel length to ensure category performance and on possible Power over Ethernet type (see details in datasheet).

The product's benefits

Installation

- This High Density patch cord with small diameter and ability to achieve a tight bend radius enables easy deployment in high density environment. It is especially perfect to use with 48 ports patchpanels in 1U.

Usage

- This High Density patch cord with small diameter provides an easier access for maintenance. For the safety of people , its Low Smoke Zero Halogen materials emit limited smoke and no halogen when exposed to high sources of heat.

Documentation

TECHNICAL DOCUMENTATION

 S000103743EN-04.pdf | PDF (0.06Mo)

 S000103743FR-04.pdf | PDF (0.07Mo)

Agreements & Certificates

 LGRP-00224-V03.01-FR.pdf | PDF (0.91Mo)

 LGRP-00224-V03.01-EN.pdf | PDF (0.94Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0985.pdf | PDF (0.12Mo)