

# Product sheet



MOSAIC™ LEGRAND

RJ45 socket category 6A UTP 1 module Mosaic white with orange shutter

REF. 076527 | EAN. 3245060765279

[> Visit e-catalogue](#)

## Product characteristics

- RJ45 Cat 6A : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 1 module
- White with orange shutter

## Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

## The product's benefits

### Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

### Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

### Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

## Documentation

### TECHNICAL DOCUMENTATION

 [F01436EN-02.pdf](#) | PDF (2.27Mo)





### Agreements & Certificates

 [LGRP-01330-V02.01-FR.pdf](#) | PDF (0.81Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_1188.pdf](#) | PDF (0.12Mo)

 [ex223001\\_0981.pdf](#) | PDF (0.11Mo)

-  LGRP-01330-V02.01-EN.pdf | PDF (0.82Mo)
-  LGRP-00420-V01.01-EN.pdf | PDF (0.63Mo)
-  AoC-CL2\_Cat6A\_UTP\_32787\_ac1171013 | (0.08Mo)
-  AoC-PL2\_Cat6A\_UTP\_32787\_ac1171012 | (0.08Mo)