

# Product sheet



MOSAIC™ LEGRAND

RJ45 socket with retractable cord 0.9m category 6 UTP  
4 modules Mosaic white

REF. 076532 | EAN. 3245060765323

[> Visit e-catalogue](#)

## Product characteristics

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector, and a retractable integrated cord to plug easily your device.
- 4 modules
- Aluminium

## Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

## The product's benefits

### Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

### Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

### Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

## Documentation

### TECHNICAL DOCUMENTATION

- [S000082622FR-00.pdf](#) | PDF (0.96Mo)
- [LE03018AB.pdf](#) | PDF (1.76Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0986.pdf](#) | PDF (0.11Mo)
- [ex223001\\_1188.pdf](#) | PDF (0.12Mo)