

Product sheet



MOSAIC™ LEGRAND

Double RJ 45 socket Mosaic category 5e UTP Soluclip accessory 3 modules white

REF. 076541 | EAN. 3245060765415

[> Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 5e UTP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connectors.
- 3 modules
- White

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- RJ 45 connectors are equipped with a locking nut that does not require the use of a specific tool and which enables re-cabling in the event of error. This system allows the wire pairs to be spread easily before mounting them on the connector.

Usage

- Very good endurance: 2500 movements (plug insertion/withdrawal).

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

 [F00948EN-05.pdf](#) | PDF (1.93Mo)

 [F00948FR-05.pdf](#) | PDF (1.94Mo)





 [LE01557AJ.pdf](#) | PDF (1.55Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_1189.pdf](#) | PDF (0.11Mo)

 [ex223001_0992.pdf](#) | PDF (0.08Mo)

Agreements & Certificates

-  AoC-PL2_C5e_UTP_32751_ac1181027 (H | (0.07Mo)
-  AoC-SA01_SB01_ac109590 | (0.06Mo)
-  LGRP-01151-V01.01-EN.pdf | PDF (0.56Mo)
-  AoC-CL2_C5e_UTP_32751_ac1181028 | (0.07Mo)