

Product sheet



MOSAIC™ LEGRAND

Double RJ 45 socket Mosaic category 6 UTP Soluclip accessory 3 modules white

REF. 076544 | EAN. 3245060765446

[> Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6 UTP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connectors.
- 3 modules
- White

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- RJ 45 connectors are equipped with a locking nut that does not require the use of a specific tool and which enables re-cabling in the event of error. This system allows the wire pairs to be spread easily before mounting them on the connector.

Usage

- Very good endurance: 2500 movements (plug insertion/withdrawal).

Avantages



- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation











TECHNICAL DOCUMENTATION

-  [F00949FR-08.pdf](#) | PDF (0.78Mo)
-  [LE01557AJ.pdf](#) | PDF (1.55Mo)
-  [F00949EN-08.pdf](#) | PDF (0.78Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_1188.pdf](#) | PDF (0.12Mo)
-  [ex223001_0986.pdf](#) | PDF (0.11Mo)

Agreements & Certificates

-  AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)
-  AoC-SA51_SB51_ac109587 | (0.06Mo)
-  AoC-CL2_Cat6UTP3275432861ac1181025 | (0.07Mo)
-  LGRP-01151-V01.01-EN.pdf | PDF (0.56Mo)
-  AoC-CL4_Cat6_UTP_32866_ac1181047 | (0.08Mo)
-  AoC-CL4_Cat6_UTP_32754_ac1181046 (| (0.08Mo)
-  AoC-PL2_Cat6_UTP_32754_ac1181024 | (0.07Mo)
-  AoC-PL2_C6_UTP_32886_ac1191056 | (0.06Mo)
-  AoC-PL3_Cat6_UTP_32754_ac1181026 | (0.07Mo)
-  AoC-CL2_C6_UTP_32886_ac1191057 | (0.06Mo)