

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket category 6A STP 1 module white

REF. 076573 | EAN. 3245060765736

[> Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6A : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 1 module
- White

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

F00950FR-08.pdf | PDF (0.84Mo)

LE01557AJ.pdf | PDF (1.55Mo)

F00950EN-08.pdf | PDF (0.83Mo)

CAD & Design specs / BIM





















CATALOGUE PAGE & OTHERS

ex223001_1188.pdf | PDF (0.12Mo)

ex223001_0981.pdf | PDF (0.11Mo)

Agreements & Certificates

 3D_LG-076573.stp | IFC (19.04Mo)
BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt | RVT (128.48Mo)
BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt | RVT (126.68Mo)

 AoC-CL4_Cat6A_STP_32869_ac1181045 | (0.08Mo)
 AoC-PL2_Cat6A_FTP_32778_ac1171014 | (0.08Mo)
 LGRP-01330-V02.01-FR.pdf | PDF (0.81Mo)
 AoC-CL2_Cat6A_STP_32777_ac1171018A | (0.08Mo)
 AoC-CL2_Cat6A_FFTP_32799_ac1171010 | (0.07Mo)
 AoC-CL2_Cat6A_FTP_32778_ac1171015 | (0.08Mo)
 AoC-PL3_Cat6A_FTP_32778_ac1171016 | (0.08Mo)
 AoC-PL2_C6A_UFTP_32884_ac1191058 | (0.06Mo)
 AoC-PL2_Cat6A_FFTP_32799_ac1171009 | (0.07Mo)
 AoC-4PPoE 2019-676 Ac Delta Force | (0.08Mo)
 AoC-PL2_Cat6A_STP_32777_ac1171017A | (0.08Mo)
 AoC-CL2_C6A_UFTP_32884_ac1191059 | (0.06Mo)
 AoC-CL2_C6A_STP_32882_ac1191063 | (0.06Mo)
 AoC-CL4_Cat6A_STP_32778_ac1181044 | (0.08Mo)
 AoC-CL2_C6A_FFTP_32883_ac1191061 | (0.06Mo)
 AoC-PL2_C6A_FFTP_32883_ac1191060 | (0.06Mo)
 LGRP-01330-V02.01-EN.pdf | PDF (0.82Mo)
 AoC-PL3_Cat6A_STP_32777_ac1171019A | (0.08Mo)
 AoC-PL2_C6A_STP_32882_ac1191062 | (0.06Mo)
 AoC-PL3_Cat6A_FFTP_32799_ac1171011 | (0.07Mo)