

Product sheet



HYPRA LEGRAND

Panel mounting socket inclined outlet Hypra-IP44
-380/415V~ - 32A - 3P+E - metal

REF. 052933 | EAN. 3245060529338



> [Visit e-catalogue](#)

Product characteristics


- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) LV panel mounting sockets 380 to 415 V~ 50/60 Hz - 32 A 3P+E - To be associated with box Cat.No 0 529 40 for surface - mounting socket or Cat.No 0 529 90 for through wiring surface mounting socket - Metal - 32 A

Documentation

TECHNICAL DOCUMENTATION

-  F00138FR-04.pdf | PDF (1.44Mo)
-  F00138EN-04.pdf | PDF (1.25Mo)

CAD & Design specs / BIM

- LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP44_400_SYMBOL.rfa | RFA (0.58Mo)
- LEGRAND_NON_INTERLOCKED_SOCKETS_SURFACE_MOUNTED_IP44_400.rfa | RFA (0.7Mo)
- LEGRAND_PRISES_NON_VERROUILLEES_ENCASTREES_IP44_400_SYMBOL.rfa | RFA (0.58Mo)
-  052933.dwg | DWG (0.13Mo)
- LEGRAND_PRISES_NON_VERROUILLEES_SAILLIES_IP44_400.rfa | RFA (0.7Mo)

Agreements & Certificates

-  OC / CB-FR_710634 | (0.7Mo)