

# Product sheet



## HYPRA LEGRAND

Panel mounting socket Hypra - IP 66/67-55 - 380/415 V~ - 125A - 3P+N+E - plastic

REF. 059513 | EAN. 3245060595135

> [Visit e-catalogue](#)

## Product characteristics

- Hypra IP 66/67 - 55 plastic - increased safety - LV 16 to 125 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP according to IEC 60529 - IK 09 : Plastic - Self - extinguishing : 850°C (support of active parts) / 650°C (plastic housing) LV 380 to 415 V~ 50/60 Hz Panel mounting sockets 3P+N+E - To associate with Cat. No 0 522 29 for surface mounting - To associate with Cat. No 0 522 89 for through wiring surface mounting - 125 A - inclined outlet

## Documentation

### TECHNICAL DOCUMENTATION

- F00130EN-07.pdf | PDF (1.29Mo)
- LE03763AA.pdf | PDF (0.13Mo)
- F00130FR-07.pdf | PDF (1.5Mo)
- LE09818AA.pdf | PDF (0.67Mo)

### CAD & Design specs / BIM

- LEGRAND\_NON\_INTERLOCKED\_SOCKETS\_FLUSH\_MOUNTED\_IP66\_400\_SYMBOL.rfa | RFA (0.56Mo)
- LEGRAND\_PRISES\_NON\_VERROUILLEES\_ENCASTREES\_IP66\_400.rfa | RFA (0.52Mo)
- LEGRAND\_NON\_INTERLOCKED\_SOCKETS\_SURFACE\_MOUNTED\_IP66\_400\_SYMBOL.rfa | RFA (0.56Mo)
- LEGRAND\_PRISES\_NON\_VERROUILLEES\_SAILLIES\_IP66\_400\_SYMBOL.rfa | RFA (0.56Mo)
- LEGRAND\_NON\_INTERLOCKED\_SOCKETS\_FLUSH\_MOUNTED\_IP66\_400.rfa | RFA (0.51Mo)
- LEGRAND\_PRISES\_NON\_VERROUILLEES\_ENCASTREES\_IP66\_400\_SYMBOL.rfa | RFA (0.56Mo)

## Agreements & Certificates

- LGRP-00200-V01.01-EN.pdf | PDF (0.71Mo)