

Product sheet



P 17 TEMPRA LEGRAND

Panel mounting socket P17 - inclined outlet - IP44 - 380/415 V~ - 16 A - 3P+N+E

REF. 555189 | EAN. 3245065551891




> [Visit e-catalogue](#)

Product characteristics


- P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets Panel mounting sockets inclined outlet - Can be fixed on plain faceplates or pre - drilled and on flush mounting boxes 380/415 V~ - IP 44 16 A - 3P+N+E

Documentation




TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)





CAD & Design specs / BIM

- No_interlocked_sockets_380_415V.rfa | RFA (1.59Mo)
-  555189.dwg | DWG (0.26Mo)
- Prises_non_verrouillées_380_415V.rfa | RFA (1.59Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0529.pdf | PDF (0.05Mo)
-  ex223001_0530.pdf | PDF (0.05Mo)
-  ex223001_0525.pdf | PDF (0.12Mo)
-  ex223001_0531.pdf | PDF (0.06Mo)

Agreements & Certificates

-  CCC-CQC2016010203837680 | (3.46Mo)
-  LGRP-2014-111-V1-EN.pdf | PDF (1.02Mo)
-  IMQ-CA02.05950 | (0.42Mo)
-  OC / CB-FR_710665 | (0.7Mo)