

Product sheet



P 17 TEMPRA LEGRAND

Panel mounting socket P17 Pro - IP66/67 - 380/415 V~
- 63 A - 3P+E

REF. 555588 | EAN. 3414970735027

[> Visit e-catalogue](#)

Product characteristics

- P 17 Tempra Pro IP 66/67 LV 63 and 125 A Panel mounting sockets - Can be fixed on the faceplates Cat.Nos 0 577 17/19380/415 V~ - 63 A - 3P+E

Documentation

TECHNICAL DOCUMENTATION

 F02385FR-01.pdf | PDF (2.98Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

 F02385EN-01.pdf | PDF (1.98Mo)

CAD & Design specs / BIM

No_interlocked_sockets_380_415V.rfa | RFA (1.59Mo)

Prises_non_verrouillées_380_415V.rfa | RFA (1.59Mo)

 555588.dwg | DWG (0.14Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0535.pdf | PDF (0.06Mo)

 ex223001_0528.pdf | PDF (0.13Mo)

 ex223001_0534.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-FR_706516 | (1.27Mo)

 LGRP-00204-V01.01-EN.pdf | PDF (0.77Mo)

 CCC-CQC2018010203055869 | (2.36Mo)