

# Product sheet



## P 17 TEMPRA LEGRAND

Mobile socket P17 - IP66/67 - 200/250 V~ - 16 A - 2P+E

REF. 555304 | EAN. 3245065553048




[> Visit e-catalogue](#)

## Product characteristics

- P 17 Tempra Pro IP 66/67 LV 16 and 32 A Mobile sockets - Supplied unlocked 200/250 V~ - 16 A - 2P+E

## Documentation

### TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)





### CAD & Design specs / BIM

-  555304.dwg | DWG (0.14Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0527.pdf | PDF (0.11Mo)
-  ex223001\_0533.pdf | PDF (0.07Mo)
-  ex223001\_0534.pdf | PDF (0.06Mo)

### Agreements & Certificates

-  LGRP-2014-110-V1-EN.pdf | PDF (1.01Mo)
-  OC / CB-FR\_710665 | (0.7Mo)
-  CQC-CQC2016010203850867 | (1.28Mo)
-  IMQ-CA02.05953 | (0.35Mo)