

# Product sheet



P 17 TEMPRA LEGRAND

Mobile socket P17 - IP44 - 380/415 V~ - 16 A - 3P+N+E

REF. 555109 | EAN. 3245065551099

[> Visit e-catalogue](#)

## Product characteristics


- P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets , plugs , mobile sockets , appliance inlets and interlocked switched sockets  
Mobile sockets - Cable clamping and closing without screws - Supplied unlocked 380/415 V~ - IP 44 16 A - 3P+N+E

## Documentation


### TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)





### CAD & Design specs / BIM

-  555109.dwg | DWG (0.15Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0529.pdf | PDF (0.05Mo)
-  ex223001\_0530.pdf | PDF (0.05Mo)
-  ex223001\_0525.pdf | PDF (0.12Mo)
-  ex223001\_0531.pdf | PDF (0.06Mo)

### Agreements & Certificates

-  LGRP-2014-110-V1-EN.pdf | PDF (1.01Mo)
-  CQC-CQC2016010203850867 | (1.28Mo)
-  OC / CB-FR\_710665 | (0.7Mo)
-  IMQ-CA02.05953 | (0.35Mo)