

# Product sheet



LIVING NOW BTICINO

RJ45 socket Living Now - category 6A UTP - 1 module - White

REF. BT-KW4279C6A | EAN. 8005543621790

[> Visit e-catalogue](#)

## Product characteristics

- RJ45 Cat 6A : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- TIA 568A/B color coded contacts for standard wiring
- Equipped with a transparent protective dust cover protecting the connector.

## Recommendation / Restriction

- Compliant with ISO/IEC 11801 edition 3.0 (2017) standards. Minimum 40mm depth electrical installation box needed. Take AWG22 up to AWG26 single-core cables. Take AWG26 multicore cables. Indoor use only.

## The product's benefits

### Installation

- Shallow depth mechanism facilitating mounting into the flush-mounted box. Socket equipped with a tool less quick connector for intuitive and reliable wiring.

### Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

### Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

## Documentation

### TECHNICAL DOCUMENTATION

 F03439EN-01.pdf | PDF (0.78Mo)

### CAD & Design specs / BIM

Bticino\_appareillage\_Living\_Now\_2023\_FR.rvt | RVT (66.08Mo)

Bticino\_Wiring\_device\_Living-Now\_2022\_EN.rvt | RVT (149.57Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0774.pdf | PDF (0.09Mo)

### Agreements & Certificates

 LGRP-01906-V01.01-EN.pdf | PDF (1.14Mo)

 LGRP-01906-V01.01-FR.pdf | PDF (1.12Mo)