

# Product sheet



LEGRAND

Line tap - non-shear - w/o feet - capacity per tap 2x25 mm<sup>2</sup> - hexagonal head

REF. 034033 | EAN. 3245060340339

[> Visit e-catalogue](#)

## Product characteristics

- Line taps and equipotential bonding connectors  
Line taps  
Non-shear line taps - Hexagonal head - Without feet - Capacity per tap : 2 x 25 mm<sup>2</sup> - Width of slot : 7.4 max. cable Ø in mm - Overall height : 49 mm

## Documentation

### TECHNICAL DOCUMENTATION

 F00003-01fr.pdf | PDF (0.04Mo)

 F00003-01en.pdf | PDF (0.04Mo)

 0064U92-01.pdf | PDF (0.01Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0820.pdf | PDF (0.22Mo)