

# Product sheet



NYLBLOC™ LEGRAND

Connection strip Nylbloc - capacity 16 mm<sup>2</sup> - max. current 76 A - black

REF. 034217 | EAN. 3245060342173

[> Visit e-catalogue](#)

## Product characteristics

- Nylbloc™ - connection strips and connectors without screws Nylbloc connection strips - 12 elements with captive screws - Supplied with screws undone - Flame retardant polypropylene (- 25 °C to + 100 °C) - Ambient temperature from - 25 °C to + 55 °C (T 55) - Conform to EN 60998 - 2 - 1 and EN 60664 - 1 - Self - extinguishing to EN 60695 - 2 - 11 at 850° - Insulation voltage : 250 V according to EN 60 998 - 2 - 1 - Use at 400 V integrated in a series of products that comply with the requirements of EN 60664 - 1, pollution degree 2, overload category III - Black - Rated capacity : 16 mm<sup>2</sup>mm<sup>2</sup> - Hole Ø : 5.5 mm - Max current : 76 A

## Documentation

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0819.pdf](#) | PDF (0.1Mo)

### Agreements & Certificates

 [VDE-40018574](#) | (0.88Mo)

 [AENOR-030/000810](#) | (0.62Mo)

 [IMQ-EN643](#) | (0.61Mo)

 [NF-650672A](#) | (0.18Mo)