

Product sheet



ARTEOR™ LEGRAND

RJ45 Category 6 UTP Arteor socket - 1 module - champagne

REF. 570057 | EAN. 3414970924551


[> Visit e-catalogue](#)

Product characteristics


- Arteor RJ 45 sockets - With LCS² connector with fast connection thanks to integrated crimping - Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables - Contacts marked with dual colour code and wiring schemes T568 A and T568 B - Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173 - 1 and TIA/EIA 568 C - Mechanisms supplied with rocker plates , to be equipped with support frames and plates
- Cat. 6 socketsUTP - 1 module - Champagne

Documentation




TECHNICAL DOCUMENTATION

-  F00973EN-07.pdf | PDF (1.47Mo)
-  LE02894AJ.pdf | PDF (2.05Mo)
-  F00973FR-07.pdf | PDF (0.82Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0580.pdf | PDF (0.12Mo)
-  ex223001_0987.pdf | PDF (0.09Mo)
-  ex223001_0876.pdf | PDF (0.1Mo)

Agreements & Certificates

-  AoC-PL2_C6_UTP_32886_ac1191056 | (0.06Mo)
-  AoC-PL3_Cat6_UTP_32754_ac1181026 | (0.07Mo)
-  AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)
-  AoC-SA51_SB51_ac109587 | (0.06Mo)
-  AoC-CL2_C6_UTP_32886_ac1191057 | (0.06Mo)
-  AoC-CL2_Cat6UTP3275432861ac1181025 | (0.07Mo)
-  AoC-CL4_Cat6_UTP_32866_ac1181047 | (0.08Mo)
-  AoC-CL4_Cat6_UTP_32754_ac1181046 (| (0.08Mo)
-  LGRP-01108-V02.01-EN.pdf | PDF (0.83Mo)
-  AoC-PL2_Cat6_UTP_32754_ac1181024 | (0.07Mo)