

# Product sheet



SYNERGY™ LEGRAND

Synergy Authentic Double USB charger type A  
Polished Stainless steel

REF. 833244 | EAN. 3414970666604

> [Visit e-catalogue](#)

## Product characteristics

- 5Vdc, 2400mA, 12W
- Consumption in passive mode 0,1 W, overvoltages protected
- Battery picto to indicate for charging only
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- 2P+E tap-off connection via 2.5 mm<sup>2</sup> screw terminals

### Usage

- One gang to charge two portable devices such as smartphones, tablets, MP4 players, loudspeakers, watches, games consoles, power banks, ...

### Avantages

- Plate in Stainless steel rust resistance
- USB 12W ideal for optimal charging of smartphones or tablets
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### TECHNICAL DOCUMENTATION



F02314EN-00.pdf | PDF (0.1Mo)



ex223001\_0725.pdf | PDF (0.08Mo)