

# Product sheet



LEGRAND

Domestic cartridge fuse - cylindrical type 10.3 x 31.5 - 25 A - without indicator

REF. 012625 | EAN. 3245060126254

[> Visit e-catalogue](#)

## Product characteristics


- Domestic cartridge fuses
- Cylindrical 10,3 x 31.5 - Rating : 25 Amps - Voltage ~ : 400 Volts - Rupture capacity Copper : 20000 Amps - Protected section : 4 mm<sup>2</sup> - Color Indication : Blue

## Documentation

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0091.pdf](#) | PDF (0.09Mo)

### Agreements & Certificates

 [NF-656079/A1](#) | (0.67Mo)