

Product sheet



LEGRAND

Visual alarm Mosaic device - complete - IP40 / IK04 - 2 modules

REF. 040596 | EAN. 3245060405960

[> Visit e-catalogue](#)

Product characteristics


- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Visual alarm devices - Conform to EN 54 - 23 standard and CE CPR approved - Mosaic device - 2 modules - Delivered with support frame and dedicated plate - IP 40 - IK 04 - Red flashing light 2 cd synchronizable with a frequency of 1 Hz - Voltage range : 10 - 58 V - Average consumption : 12 VDC 14 mA - 24 VDC 16 mA - 48 VDC 18 mA

Documentation

TECHNICAL DOCUMENTATION

→ [LE04405AB.pdf](#) | PDF (1.47Mo)

Agreements & Certificates

 [NFSSI Composant-DL 004 B2](#) | (0.22Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0921.pdf](#) | PDF (0.05Mo)