

Product sheet



LEGRAND

Visual alarm surface mounting device - IP45 / IK07

REF. 040598 | EAN. 3245060405984

[> Visit e-catalogue](#)

Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Visual alarm devices - Conform to EN 54 - 23 standard and CE CPR approved - Surface - mounting - IP 45 - IK 07 - Red flashing light 2/10 cd synchronizable with a frequency of 1 Hz - Voltage range : 9 - 58 V - Average consumption (2 cd) : 12 V DC 14 mA - 24 V DC 16 mA - 48 V DC 18 mA - Average consumption (10 cd) : 12 V DC 38 mA - 24 V DC 40 mA - 48 V DC 42 mA

Documentation

TECHNICAL DOCUMENTATION

→ [LE04994AA.pdf](#) | PDF (1.12Mo)

Agreements & Certificates

[NFSSI Composant-DL 017 B1](#) | (0.22Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0921.pdf](#) | PDF (0.05Mo)