

Product sheet



MOSAIC™ LEGRAND

KNX 2x300W universal dimmer - din

REF. 002654 | EAN. 3245060026547

> [Visit e-catalogue](#)

Product characteristics

- 2 outputs - 300 W/VA maximum per output
- DIN 4 modules
- Mains voltage 230VAC - 50/60Hz
- Power supply from KNX bus

Recommendation / Restriction

- Configuration through ETS tool from KNX association

The product's benefits

Installation

- Connected with the BUS/KNX cable

Usage

- Each output can be controlled by a sensor and/or BUS/KNX control unit

Advantages

- Because a broad range of KNX devices communicate with each other, (even if they are from different manufacturer) KNX technology answers to high demands for smart home or building thanks to endless flexibility and personalization

Documentation

TECHNICAL DOCUMENTATION

S000094312FR-1.pdf | PDF (3.5Mo)

LE09579AB.pdf | PDF (1.08Mo)

S000094312EN-1.pdf | PDF (3.35Mo)

Agreements & Certificates

Decl. UE RED-A 3717 B | (0.2Mo)

KNX EIB-11/14236/17 | (0.19Mo)

CATALOGUE PAGE & OTHERS

ex223001_0896.pdf | PDF (0.07Mo)

Software & configurators

002654_KNXProductDIMMER2.knxprod.zip | ZIP (0.05Mo)