

Product sheet



LEGRAND

LCS³ 19" PDU - 1U - 9 x 2P+E - German standard - 16 A 1P MCB - height 2U - 3 m power supply cord with 16 A 2P+E plug

REF. 646832 | EAN. 3414971099012

[> Visit e-catalogue](#)

Product characteristics

- Legrand cabling system LCS³ energy distribution - 1U Basic Power Distribution Units (PDU) - To provide ~ electric power for IT equipment in 19" enclosures - 230 V - 50/60 Hz power supply - 1U aluminium profile - End cap with metallic brackets and cable holder shape - Quick fixing (no screws) on 19" fixing centers. Can also be installed vertically by reverting the brackets (no screws) - 2P+E outlets : - C13 and C19 standard outlets are equipped with cord locking system to avoid any accidental disconnection. Universal solution compatible with all the cords (C14 plugs for C13 and C20 plugs for C19) - French, German and British standard outlets are equipped with safety shutters - French and German standard outlets are inclined at 55° - Black modules (outlets and functions)
- 19€ Basic PDU with protection devices - MCB and RCBO support with projecting edges to avoid accidental breakdown - 3 m power supply cord with 16 A 2P+E French/German plug German standard - 9 outlets and a 16 A single pole Micro Circuit Breaker, 2U height

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-15.pdf | PDF (3.09Mo)

 S000093176FR-15.pdf | PDF (3.1Mo)

Agreements & Certificates

 LGRP-01740-V01.01-EN.pdf | PDF (0.91Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1016.pdf | PDF (0.19Mo)